



# 16" 3-High Lenticular Housing - 65101A-A

## EXPLODED VIEW




# 16" 3-High Lenticular Housing - 65101A-A

## EXPLODED VIEW PARTS LEGEND


Last updated: 03/1/2023

PART (SEE EXPLODED VIEW)	DESCRIPTION	*ITEM #	COMMENTS
1	16" 3-high dome	N/A	Can only be ordered as a whole assembled housing
2	16" 3-high dome base	N/A	Can only be ordered as a whole assembled housing
3	16" base o-ring	970002	Also available in Viton
4, 5 & 6	Locking nut assembly	65003	
7* (extra item)	Backflush end plate (2)	65105NVE	Extra add-on item(s) for use with Supradisc II backflushable media only. <b>Not included in housing base price.</b>
8	3-high center post	65104	
9*	16" deflection plate (lipped) 16" deflection plate (non-lipped)	970022C 970022C2	
10	1.5" TC gasket	570002	
11	1.5" TC clamps	570022	
12	0.5" TC gasket	570000	
13	0.5" TC clamp	570020	
14	1.5" TC pressure gauge 0-58 psi	65110PG	
15	1.5" TC tee	570062	
16	1.5" TC butterfly valve	572212	
17	0.5" TC x barb vent/drain valve	572301	
18	0.5" TC ball valve	57220	
19 & 20	1.5" elbow 90°	N/A	On later models, elbows are welded on. Older model elbows do not have drains.
21	Lenticular housing eye bolt	971165	
22* (extra item)	Intermediate plate (2)	65105NVI	Extra add-on item(s) for use with Supradisc II backflushable media only. <b>Not included in housing base price.</b>
23	0.5" TC x 0.5" hose barb	570081	<i>*Please contact us if you purchased your housing prior to 2016</i>

### OTHER RESOURCES



Lenticular Housing Product Pages  
& Operating Instructions



Lenticular Filtration Articles